

0

CMOS area image sensors

S10830

S10834

CMOS area image sensors for X-ray imaging

S10830 is CMOS area image sensor suitable for intra-oral X-ray imaging in dental diagnosis. S10830 has 1.5 megapixels (1000 \times 1500) with a pixel size of 20 \times 20 μ m. FOP (fiber optic plate) is used as an input window, making S10830 high image-quality and long-term X-ray life. S10834 is an easy-to-use X-ray imaging module using S10830 with a cable. S10830 has 14-bit ADC on chip and LVDS digital output signal. It is to contribute cost reduction in a user's system. S10831 and S10835 (1300 \times 1700 pixels) are also available.

Features

- Pixel size: 20 × 20 μm
- **■** 1000 (H) × 1500 (V) pixel format
- ➡ Frame rate: 0.9 frames/s (MCLK=20 MHz)
- → High resolution: 20 Lp/mm typ.
- **14-bit ADC (virtual dynamic range: 58 dB)**
- Image data acquisition by Vdd, Vss, MCLK and MST only
- **■** Global shutter operation
- Photodiode placed outside the active area to monitor x-ray irradiation

Applications

- Intra-oral X-ray imaging dental diagnosis
- General X-ray imaging
- Non-destructive inspection

These products are components for incorporation into medical device.

Structure

Parameter	Value	Unit
Pixel size	20 × 20	μm
Pixel pitch	20	μm
Number of effective pixels	1000 (H) × 1500 (V)	pixels
Number of light-shielded pixels	Upper part: 766, 768, 770 Lower part: 1000 × 3	pixels
Image size	20 (H) × 30 (V)	mm

■ Absolute maximum ratings

Parameter	Symbol	Value	Unit
Power supply	Vdd	-0.5 to +6	V
Input voltage	Vi	-0.5 to "Vdd + 0.5" (6 max.)	V
Consumption current	Idd	400	mA
Operating temperature	Topr	0 to +50	°C
Storage temperature	Tstg	-20 to +70	°C
Total dose irradiation	D	50	Gy

Recommended operating conditions

Parameter		Symbol	Min.	Тур.	Max.	Unit
Power supply		Vdd	4.75	5.0	5.5	V
Digital input voltage*1	High	Vsigi(H)	2.4	3.3	Vdd + 0.25	V
Digital input voltage*1	Low	Vsigi(L)	0	-	0.4	V

^{*1:} Vsigi(H) is a "High" period voltage of MST and MCLK, Vsigi(L) is a "Low" period voltage of MST and MCLK.

Electrical characteristics (Ta=25 °C, Vdd=5 V)


Para	Parameter		Min.	Тур.	Max.	Unit
Master clock pulse fre	quency	f(MCLK)	1 M	20 M	40 M	Hz
Digital output format		-	LV	'DS differential outp	out	-
Digital output	Image sensor*2	f(DO)	-	f(MCLK)	-	Hz
frequency	Trigger photodiode*3	f(DO)	-	f(MCLK)/56	-	П
	Digital output voltage*4		-	350	-	mV
Digital output rise time*4 *5		tr(DO)	-	2	5	ns
Digital output fall time	Digital output fall time*4 *5		-	2	5	ns
Video data rate	Image sensor*6	VR	-	f(MCLK)/14	-	Hz
video data rate	Trigger photodiode	VR2	-	f(MCLK)/7168	-	Hz
Start pulse interval*7		T(ST-I)	22.7 M	-	-	MCLK
Integration time	Image sensor*8		PW(MST) + 394/f(MCLK)			S
Integration time	Trigger photodiode*9	-	6608/f(MCLK)			S
C	Image sensor*10	P1	-	55	110	mA
Consumption current	Trigger photodiode*11	P2	-	25	50	mA

^{*2:} Refer to "Timing chart", Image data readout.

Integration time = 10 ms + 394/20 M = 10.0197 ms


Integration time = $6608/20 \text{ M} = 330.4 \mu \text{s}$

- Resolution (S10834)



Spatial frequency (line pairs/mm)

- Response (S10834)



Absorbed dose (µGy)

KMPDB0359EA

^{*3:} Refer to "Timing chart", Trigger photodiode data readout.

^{*4:} The output voltage difference between LVDS differential terminals with 100 Ω termination

^{*5:} The time in output from 10% to 90% or from 90% to 10% with 2 m long cable

^{*6:} It takes 14 master clock pulse cycles to read out 1 pixel

^{*7:} It takes 22.7 M master clock pulse cycles to read out 1 frame of an image. The readout of the next frame must be started after finishing the readout of previous frame.

^{*8:} Refer to "Timing chart", PW(MST) is "Low" pulse width of MST (master start pulse).

e.g.) When the PW(MST) is 10 ms and f(MCLK) is 20 MHz:

^{*9:} Refer to "Timing chart", The trigger photodiode is output every 7168 MCLK cycles. The integration time is 6608 MCLK cycles, and 560 MCLK cycles are used for the reset period of trigger photodiode.

e.g.) When the f(MCLK) is 20 MHz:

^{*10:} The consumption current of image sensor chip only. f(MCLK)=20 MHz

^{*11:} The consumption current of image sensor chip only. Without 100 Ω termination (see "Output format" in P.7). f(MCLK)=20 MHz

■ Electrical and optical characteristics (image sensor, Ta=25 °C, Vdd=5 V)

Parameter		Symbol	Min.	Тур.	Max.	Unit	
Dark output voltage (effective pixel)*12		Vdark	-	50	120	mV/s	
Dark output v	voitage (errecti	ve pixei)	Ddark	-	200	490	LSB/s
Caturation ou	thut voltage		Vsat	0.8	1.2	-	V
Saturation ou	itput voitage		Dsat	3280	4900	-	LSB
Random noise	0*13		VRN	-	1500	4500	μV rms
Kandom noise			DRN	-	6.2	18	LSB rms
Dynamic range*14		DR	45	58	-	dB	
Sensitivity*15			VRES	2.3	3.4	4.5	mV/μGy
Selisitivity			DRES	9.4	14	18	LSB/µGy
Saturation do			Lsat	180	350	530	μGy
Photo respon	se non-uniforn	nity* ¹² * ¹⁶	PRNU	-	-	±30	%
	Point	White spot		-	-	20	
Blemish	defect*17	Black spot		-	-	20	
Big cluster defect*19		t*18	-	-	-	3	_
			-	-	0		
Defect line*20		DL	-	-	15	lines	
X-ray resoluti	on		Reso	15	20	-	Lp/mm

^{*12:} Average value. Excluding defect pixels.

*14: Dynamic range = $20 \times \log \left(\frac{\text{Saturation output voltage}}{\text{Random noise}} \right)$

V: average of pixel outputs, ΔV : difference between V and min. or max. output

➡ Electrical and optical characteristics (trigger photodiode, Ta=25 °C, Vdd=5 V)

Parameter	Symbol	Min.	Тур.	Max.	Unit
Saturation voltage	Vsat	-	2.2	2.9	V
Saturation voitage	Dsat	-	450	590	LSB
Random noise	VRN	-	10	-	mV rms
Random noise	DRN	-	2	-	LSB rms
Sensitivity* ²¹	VRES	-	6.8×10^{2}	-	mV/μGy
Sensitivity	DRES	-	200	-	LSB/µGy
Offset of A/D converter	-	-	430	-	LSB

^{*21:} Integration time=330 μ s, f(MCLK)=20 MHz

■ Electrical and optical characteristics (A/D converter, Ta=25 °C, Vdd=5 V)

Parameter	Symbol	Image sensor	Trigger photodiode	Unit
Resolution	RESO	14	10	bit
Connection time	tCON	1/14 × f(MCLK)	1/7168 × f(MCLK)	S
Conversion voltage range	-	0 to 4	0 to Vdd	V



^{*13:} Integration time = 1 s

^{*15: 60} kV tube voltage, no Al plate at X-ray emission

^{*16:} PRNU (%) = $\Delta V / V \times 100$


^{*17:} White spot > 1.2 V/s (4900 LSB/s) at effective pixel: 10 times of the maximum of dark output Black spot > 50% reduction in response relative to adjacent pixels, measured at half of the saturation output

^{*18:} Continuous 2 to 9 point defects

^{*19:} Continuos 10 or more point defects. (except a defect line)


^{*20:} A defect line consists of 10 or more point defects in 1 pixel width.

Block diagram



KMPDC0356EB


Timing chart



- (A) Continuously checking some X-ray radiation with monitoring the data of trigger photodiode by an external circuit.
- (B) The MST should be set at low and integration of each pixel is to start when X-ray input is detected. The Integration time is almost same as the low width of the MST. It can be controlled by an external circuit (software, firmware, etc.).
- (C) Just after the MST is set at high, the integration is to finish and readout starts.
- (D) Each readout row has a header part, which consists of 28 high levels of the OUTDATA.
- (E), (F) After completion readout, the OUTCLK and the OUTDATA automatically move to state of trigger photodiode.


KMPDC0357EB






Note: All on-chip timing circuits are reset at rise of MST, and the operations of trigger photodiode readout are stopped at this time.





(F) Image readout end (trigger photodiode)



Note: Just after image data is finished, the 1st readout of trigger photodiode is not valid, because integration time is shorter than others.



□ Output format (Ta=25 °C, Vdd=5 V)

■ With 100 Ω termination (LVDS output mode)


Parameter	Symbol	Min.	Тур.	Max.	Unit
Differential output swing	Vod	247	-	454	mV
Offset voltage	Vos	-	1.2	-	V
Current (100 Ω termination)	I100	-	3.5	-	mA

■ Without 100 Ω termination (CMOS output mode)

Parameter		Symbol	Min.	Тур.	Max.	Unit
Output voltage	High level	Vod	-	2.4	-	V
	Low level	Vos	-	0	0.4	V

Dimensional outline (unit: mm)

S10830




KMPDA0266EB

■ Pin connections

Pili connectio	115		
Pin no.	Description	I/O	Function
1	Vdd	I	Power supply voltage (5 V)
2	Vss	I	Ground
3	Outdata a	0	Video output signal (LVDS, positive)
4	Reserve	-	
5	Outdata b	0	Video output signal (LVDS, negative)
6	Reserve	-	
7	Outclk a	0	Trigger signal (LVDS, positive)
8	Reserve	-	
9	Outclk b	0	Trigger signal (LVDS, negative)
10	Reserve	-	
11	MST	I	Master start signal
12	Reserve	-	
13	MCLK	I	Master clock signal
14	Reserve	-	


S10834

■ Entire view




KMPDA0252EB

■CMOS sensor



Photosensitive area



Horizontal shift register scanning direction

KMPDC0327FC

Information described in this material is current as of September, 2011.

Product specifications are subject to change without prior notice due to improvements or other reasons. Before assembly into final products, please contact us for the delivery specification sheet to check the latest information.

Type numbers of products listed in the delivery specification sheets or supplied as samples may have a suffix "(X)" which means preliminary specifications or a suffix "(Z)" which means developmental specifications.

The product warranty is valid for one year after delivery and is limited to product repair or replacement for defects discovered and reported to us within that one year period. However, even if within the warranty period we accept absolutely no liability for any loss caused by natural disasters or improper product use.

Copying or reprinting the contents described in this material in whole or in part is prohibited without our prior permission.

HAMAMATSU

www.hamamatsu.com

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Higashi-ku, Hamamatsu City, 435-8558 Japan, Telephone: (81) 53-434-3311, Fax: (81) 53-434-5184

U.S.A.: Hamamatsu Corporation: 360 Footbill Road, P.O.Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1) 908-231-0960, Fax: (1) 908-231-1218
Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, P-82211 Herrsching am Ammersee, Germany, Telephone: (49) 8152-375-6, Fax: (49) 8152-365-8

France: Hamamatsu Photonics France S.A.R.L.: 19, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: 33-(1) 69 53 71 00, Fax: 33-(1) 69 53 71 10

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordshire AL7 1BW, United Kingdom, Telephone: (44) 1707-294888, Fax: (44) 1707-325777

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen L1, SE-171 41 Solna, Sweden, Telephone: (46) 8-509-031-01

Italy: Hamamatsu Photonics Italia S.R.L.: Strada della Moia, 1 int. 6, 20020 Arese, (Milano), Italy, Telephone: (39) 02-935-81-733, Fax: (39) 02-935-81-741