


LVDS 5 x 3.2mm 2.5V Oscillator

Model: FXO-LC52 SERIES

Freq: 0.75 MHz to 1.0GHz

Features

- XTREMELY Low Jitter
- Low Cost
- XPRESS Delivery
- Frequency Resolution to six decimal places
- Stabilities to ± 20 PPM
- -20 to +70℃ or -40 to +85℃ operating temperatures
- Tri-State Enable / Disable Feature
- Industry Standard Package, Footprint & Pin-Out
- Fully RoHS compliant
- Gold over Nickel Termination Finish
- Serial ID with Comprehensive Traceability



For more information -- Click on the drawing

Description

The Fox XPRESSO Crystal Oscillator is a breakthrough in configurable Frequency Control Solutions. XPRESSO utilizes a family of proprietary ASICs, designed and developed by Fox, with a key focus on noise reduction technologies.

The 3rd order Delta Sigma Modulator reduces noise to the levels that are comparable to traditional Bulk Quartz and SAW oscillators. The ASICs family has ability to select the output type, input voltages, and temperature performance features.

With the XPRESS lead-time, low cost, low noise, wide frequency range, excellent ambient performance, XpressO is an excellent choice over the conventional technologies.

Finished XPRESSO parts are 100% final tested.



Rev.03/31/2008





Applications

- ANY application requiring an oscillator
- SONET
- Ethernet
- Storage Area Network
- Broadband Access
- Microprocessors / DSP / FPGA
- Industrial Controllers
- Test and Measurement Equipment
- Fiber Channel

Contents

| | page |
|---|-----------------|
| Model Selection & Part Number Guide | 2 |
| Electrical Characteristic | 3 |
| Absolute Maximums | 3 |
| Output Wave Characteristics | 4 |
| Phase Noise | 5 |
| Jitter | 5 |
| Pin Assignment | 6 |
| Recommended Circuit | 6 |
| Reflow | 6 |
| Mechanical Drawing and Pad Layout | 7 |
| Tape and Reel Specification | 8 |
| Label | 8 |
| Traceability – LOT Number & Serial Identificatior | າ 9 |
| RoHS Material Declaration | 10 |
| SGS Report 11 a | & 12 |
| Mechanical Test | 13 |
| Burn-In Test | 13 |
| MTTF / FITS calculations | 14 |
| Other XPRESSO Links | 15 |
| Fox Contact Information | 15 |





Model Selection Guide & Fox Part Number

STEP #1: Customer selects the Model Description and provides to Fox Customer Service

Model Description

FXO - LC 5 2 6 R - 622.08 Frequency (in MHz) Resolutions to 6 places past the decimal point C = Ceramic $0 = \pm 100 \text{ PPM}$ $5 = 5 \times 3.2 \text{mm}$ 3 = 3.3 V

blank = -20℃ to +70℃

L = LVDS

H = HCMOS

Q = Quartz

 $7 = 7 \times 5 \text{mm}$

2 = 2.5 V

 $5 = \pm 50 \text{ PPM}$

R = -40°C to +85°C

P = LVPECL

 $6 = \pm 25 \text{ PPM}$


 $8 = \pm 20 \text{ PPM} (-20 \sim +70 \degree)$

M = LVDS (pin 2 E/D)

Q = LVPECL (pin 2 E/D) $X = HCMOS (comp 2^{nd} Output)$

STEP #2: The Fox Customer Service team provides a customer specific Part Number for use on their Bill Of Materials (BOM).

Fox Part Number (The assigned Fox Part Number must be on the BOM – not the above Model Description) (This will ensure receipt of the proper part)



This example, FXO-LC526R-622.08 = LVDS Output, Ceramic, 5 x 3.2mm Package, 2.5V, ±25 PPM Stability, -40 to +85℃ Temperature Range, at 622.08 MHz





| Electrical Characteristics | | | |
|--------------------------------|-----------------|--|---|
| Parameters | Symbol | Condition | Maximum Value (unless otherwise noted) |
| Frequency Range | Fo | | 0.750 MHz to 1.0 GHz |
| Frequency Stability 1 | | | 100, 50, 25, & 20 ppm |
| Temperature Range | T _O | Standard operating Optional operating Storage | -20℃ to +70℃ -40℃ to +85℃ -55℃ to +125℃ |
| Supply Voltage | V _{DD} | Standard | 2.5V ± 5% |
| Input Current (@ 100 Ohm LOAD) | I _{DD} | 0.75 ~ 20.000 MHz 20.000+ ~ 220.000 MHz 220.000+ ~ 630.000 MHz 630.000+ MHz ~ 1.000 GHz | 26 mA 34 mA 44 mA 65 mA |
| Output Load | | Standard | 100 Ohms Typ. |
| Start-Up Time | Ts | | 10 mS |
| Output Enable / Disable Time | | | 100 nS |
| Moisture Sensitivity Level | MSL | JEDEC J-STD-20 | 1 |
| Termination Finish | | | Au |

Note 1 - Stability is inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock and vibration.

Absolute Maximum Ratings (Useful life may be impaired. For user guidelines only, not tested. Operation is only guaranteed for voltage and temperature specifications in Electrical Characteristics section.) **Maximum Value Parameters Symbol Condition** (unless otherwise noted) Input Voltage V_{DD} -0.5V to +5.0V Operating Temperature -55℃ to +105℃ $\mathsf{T}_{\mathsf{AMAX}}$ -55℃ to +125℃ Storage Temperature $\mathsf{T}_{\mathsf{STG}}$ Junction Temperature 150℃ **ESD Sensitivity HBM** Human Body Model > 1 kV






| Output Wave Characteristics | | | |
|--|-----------------|------------------------------|--|
| Parameters | Symbol | Condition | Maximum Value (unless otherwise noted) |
| Differential Output Voltage | V _{OD} | 0.75 MHz to 1.0 GHz | 0.4V Typ. |
| Output Offset Voltage | Vos | Volts DC | 1.25V Typ |
| Output Symmetry (See Drawing Below) | | @ 50% V _{P-P} Level | 45% ~ 55% |
| Output Enable (PIN # 1) Voltage Note1 | V_{IH} | | ≥ 70% V _{DD} |
| Output Disable (PIN # 1) Voltage Note1 | V _{IL} | | ≤ 30% V _{DD} |
| Cycle Rise Time (See Drawing Below) | T _R | 20%~80% Vp-p | 400 pS |
| Cycle Fall Time (See Drawing Below) | T _F | 80%~20% Vp-p | 400 pS |


Note1 An optional PIN # 2 as Enable / Disable is available – see Model Selection Guide (page 2)

Rise Time / Fall Time Measurements




Oscillator Symmetry

Ideally, Symmetry should be 50/50 for 1/2 period -- Other expressions are 45/55 or 55/45









Jitter is frequency dependent. Below are typical values at select frequencies.

| LVDS Phase Jitter & Time Interval Error (TIE) | | | |
|---|----------------------------------|------------------------------------|--------|
| Frequency | Phase Jitter (12kHz to 20MHz) | TIE (Sigma of Jitter Distribution) | Units |
| 62.5 MHz | 2.12 | 3.1 | pS RMS |
| 156.25 MHz | 1.04 | 3.5 | pS RMS |
| 212.5 MHz | 1.35 | 4.2 | pS RMS |
| 622.08MHz | 1.30 | 3.7 | pS RMS |

Phase Jitter is integrated from HP3048 Phase Noise Measurement System; measured directly into 50 ohm input; V_{DD} = 2.5V.

TIE was measured on LeCroy LC684 Digital Storage Scope, directly into 50 ohm input, with Amherst M1 software; V_{DD} = 2.5V.

Per MJSQ spec (Methodologies for Jitter and Signal Quality specifications)

| LVDS Random & Deterministic Jitter Composition | | | |
|--|-------------------------|--------------------|-------------------------------------|
| Frequency | Random (Rj) (pS RMS) | Deterministic (Dj) | Total Jitter (Tj) (14 x Rj) + Dj |
| 62.5 MHz | 1.35 | 8.4 | 27.6 pS |
| 156.25 MHz | 1.40 | 9.2 | 29.2pS |
| 212.5 MHz | 1.42 | 10.9 | 31.2 pS |
| 622.08 MHz | 1.18 | 10.4 | 27.2 pS |

Rj and Dj, measured on LeCroy LC684 Digital Storage Scope, directly into 50 ohm input, with Amherst M1 software.

Per MJSQ spec (Methodologies for Jitter and Signal Quality specifications)







| Pin | Pin Description and Recommended Circuit | | | |
|------|---|--------|---|--|
| Pin# | Name | Туре | Function | |
| 1 | E/D ¹ | Logic | Enable / Disable Control of Output (0 = Disabled) | |
| 2 | NC | | No Connection – Leave OPEN | |
| 3 | GND | Ground | Electrical Ground for V _{DD} | |
| 4 | Output | Output | LVDS Oscillator Output | |
| 5 | Output 2 | Output | Complementary LVDS Output | |
| 6 | V _{DD} 2 | Power | Power Supply Source Voltage | |

NOTES:


- Includes pull-up resistor to V_{DD} to provide output when the pin (1) is No Connect.
- ² Installation should include a 0.01μF bypass capacitor placed between V_{DD} (Pin 6) and GND (Pin 3) to minimize power supply line noise.



Terminations as viewed from the Top NOTE: XPRESSO LVDS XOs are designed to fit on Industry Standard, 6 pad layouts




| Enable / Disable Control | |
|---|---------------------------|
| Pin # 1 (state) | Output (Pin # 4, Pin # 5) |
| OPEN (No Connection) | ACTIVE Output |
| "1" Level V _{IH} ≥ 70% V _{DD} | ACTIVE Output |
| "0" Level V _{IL} ≤ 30% V _{DD} | High Impedance |






Mechanical Dimensional Drawing & Pad Layout



Actual part marking is depicted.

See **Traceability** (pg. 9) for more information

Recommended Solder Pad Layout



Note: XPRESSO LVDS XOs are designed to fit on Industry standard, 6 pad, layouts.

Pin Connections

#1) E/D #4) Output

#2) NC #5) Output 2


#3) GND #6) V_{DD}

Drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, reference pin shape, etc. may vary







Tape and Reel Dimensions




1k Reel Dimensions in mm



2k Reel Dimensions in mm



Labeling (Reels and smaller packaging are labeled with the below)





An additional identification code is contained internally if tracking should ever be necessary





Traceability - LOT Number & Serial Identification

LOT Number

The LOT Number has direct ties to the customer purchase order. The LOT Number is marked on the "Reel" label, and also stored internally on non-volatile memory inside the XPRESSO part. XPRESSO parts that are shipped Tape and Reel, are also placed in an Electro Static Discharge (ESD) bag and will have the LOT Number labeled on the exterior of the ESD bag.

It is recommended that the XPRESSO parts remain in this ESD bag during storage for protection and identification.

If the parts become separated from the label showing the LOT Number, it can be retrieved from inside one of the parts, and the information that can be obtained is listed below:

- Customer Purchase Order Number
- Internal Fox Sales Order Number
- Dates that the XPRESSO part was shipped from the factory
- The assigned customer part number
- The specification that the part was designed for

Serial Identification

The Serial ID is the individualized information about the configuration of that particular XPRESSO part. The Serial ID is unique for each and every XPRESSO part, and can be read by special Fox equipment.

With the Serial ID, the below information can be obtained about that individual, XPRESSO part:

- Equipment that the XPRESSO part was configured on
- Raw material used to configure the XPRESSO part
- Traceability of the raw material back to the foundries manufacturing lot
- Date and Time that the part was configured
- Any optimized electrical parameters based on customer specifications
- Electrical testing of the actual completed part
- Human resource that was monitoring the configuration of the part

Fox has equipment placed at key Fox locations World Wide to read the Lot Identification and Serial Number of any XPRESSO part produced and can then obtain the information from above within 24 hours





RoHS Material Declaration

| | Material Name | Component | Content | Content | |
|-----------|------------------|--|-----------|------------|--------------|
| | | | (mg) | (w t %) | (CAS Number) |
| Cover | Kovar | Nickel (Ni) | 1.890 | 3.09% | 7440-02-0 |
| | | Cobalt (Co) | 1.113 | 1.82% | 7440-48-4 |
| | | Iron (Fe) | 3.540 | 5.78% | 7439-89-6 |
| Base | Ceramic | Alumina (Al ₂ O ₃) | 35.484 | 57.98% | 1344-28-1 |
| | | Silicon Oxide (SiO ₂) | 1.733 | 2.83% | 14808-60-7 |
| | | Chromium Oxide (Cr ₂ O ₃) | 0.268 | 0.44% | 1308-38-9 |
| | | Molybdenum Oxide (MoO ₂) | 0.364 | 0.59% | 18868-43-4 |
| | | Magnesium Oxide (MgO) | 0.234 | 0.38% | 1309-48-4 |
| | | Calcium Oxide (CaO) | 0.253 | 0.41% | 1305-78-8 |
| | + Metallization | Tungsten (W) | 6.290 | 10.28% | 7440-33-7 |
| | | Molybdenum (Mo) | 0.195 | 0.32% | 7439-98-7 |
| | + Nickel Plating | Nickel (Ni) | 0.810 | 1.32% | 7440-02-0 |
| | | Cobalt (Co) | 0.203 | 0.33% | 7440-48-4 |
| | + Gold Plating | Gold (Au) | 0.281 | 0.46% | 7440-57-5 |
| | +Seal ring | Iron (Fe) | 2.438 | 3.98% | 7439-89-6 |
| | | Nickel (Ni) | 1.309 | 2.14% | 7440-02-0 |
| | | Cobalt (Co) | 0.768 | 1.25% | 7440-48-4 |
| | +silver solder | Silver (Ag) | 1.191 | 1.95% | 7440-22-4 |
| | | Copper (Cu) | 0.210 | 0.34% | 7440-50-8 |
| I C | I C | Aluminum (Al) | 0.0021 | 0.00343% | 7429-90-5 |
| | | Silicon (Si) | 0.950 | 1.55% | 7440-21-3 |
| | Gold | Gold (Au) | 0.480 | 0.784% | 7440-57-5 |
| | Adhesive | Silver (Ag) | 0.000210 | 0.000343% | 7440-22-4 |
| | | Ероху | 0.0000700 | 0.0001144% | |
| Crystal | Crystal | Silicon Dioxide (SiO ₂) | 1.170 | 1.91% | 14808-60-7 |
| Electrode | | Silver (Ag) | 0.019 | 0.0310% | 7440-22-4 |
| | Nickel (Ni) | 0.000159 | 0.000260% | 7440-02-0 | |
| | Adhesive | Silver (Ag) | 0.00037 | 0.000605% | 7440-22-4 |
| | | Silicon (Si) | 0.000125 | 0.000204% | 7440-21-3 |
| TOTAL | | | 61.196 | 100.00% | |





3rd Party (SGS) Material Report



Test Report No. 2053204/EC Date : Mar 01 2006 Page 1 of 2

FOX ELECTRONICS 5570 ENTERPRISE PARKWAY FT. MYERS, FL 33905

Report on the submitted sample said to be CERAMIC SEAM SEAL OSCILLATOR.

SGS Job No. : 1981176

Supplier / Manufacturer : FOX ELECTRONICS Sample Receiving Date : FEB 17 2006 Testing Period : FEB 18 - 24 2006

Test Requested: 1) To determine the Cadmium Content in the submitted sample.

- To determine the Lead Content in the submitted sample.
- To determine the Mercury Content in the submitted sample.
- To determine the Hexavalent Chromium Content on the submitted sample.
- To determine PBBs (polybrominated biphenyls) and PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method : 1-3) With reference to EPA Method 3051/3052.

Analysis was performed by Inductively Coupled Argon Plasma-Atomic

Emission Spectrometry (ICP-AES).

With reference to EPA Method 3060A & 7196A.

The sample was alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A (by UV-Vis

Spectrophotometer).

5) With reference to EPA Method 3540C/ 3550C. Analysis was performed by

GC/MS or LC/ MS.

Test Results : 1-5) Please refer to next page.

Signed for and on behalf of SGS Hong Kong Ltd

Ho Ka Ting, Family Laboratory Executive

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.

SGS Hong Kong Ltd. S/F - 8/F ß 28/F -29/F, Metropole Square, 2 On Ylu Street, Slu Lek Yuen, Shatlin, N.T., Hong Kong. t (852) 2334 4481-9 f (852) 2764 3126 www.hk.sgs.com



Party (SGS) Material Report (continued)



Test Report No. 2053204/EC Date: Mar 01 2006 Page 2 of 2

Test Results

| Test Item | 1 | Detection Limit |
|--|----|-----------------|
| 1) Cadmium (Cd) | ND | 2 ppm |
| 2) Lead (Pb) | ND | 2 ppm |
| 3) Mercury (Hg) | ND | 2 ppm |
| 4) Hexavalent Chromium (Cr ⁶⁺) | ND | 2 ppm |

(Results shown are of the total weight of samples)

Note: ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value

5)

| Flame Retardants | 1 | Detection Limit |
|---------------------------------------|----|-----------------|
| Polybrominated Biphenyls (PBBs) | | |
| Monobromobiphenyl | ND | 5 ppm |
| Dibromobiphenyl | ND | 5 ppm |
| Tribromobiphenyl | ND | 5 ppm |
| Tetrabromobiphenyl | ND | 5 ppm |
| Pentabromobiphenyl | ND | 5 ppm |
| Hexabromobiphenyl | ND | 5 ppm |
| Heptabromobiphenyl | ND | 5 ppm |
| Octabromobiphenyl | ND | 5 ppm |
| Nonabromobiphenyl | ND | 5 ppm |
| Decabromobiphenyl | ND | 5 ppm |
| Polybrominated Diphenylethers (PBDEs) | | |
| Monobromodiphenyl ether | ND | 5 ppm |
| Dibromodiphenyl ether | ND | 5 ppm |
| Tribromodiphenyl ether | ND | 5 ppm |
| Tetrabromodiphenyl ether | ND | 5 ppm |
| Pentabromodiphenyl ether | ND | 5 ppm |
| Hexabromodiphenyl ether | ND | 5 ppm |
| Heptabromodiphenyl ether | ND | 5 ppm |
| Octabromodiphenyl ether | ND | 5 ppm |
| Nonabromodiphenyl ether | ND | 5 ppm |
| Decabromodiphenyl ether | ND | 5 ppm |

Note ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value.

Sample Description:

1. Black Ceramic w/ Silvery, Golden Metal w/ Silvery Chips

*** End of Report ***

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.

SGS Hong Kong Ltd. S/F - 8/F & 28/F - 29/F, Metropole Square, 2 On Ylu Street, Slu Lek Yuen, Shatin, N.T., Hong Kong. t (852) 2334 4481-9 f (852) 2764 3126 www.hk.sgs.com






Mechanical Testing

| Parameter | Test Method |
|--------------------------|--|
| Mechanical Shock | Drop from 75cm to hardwood surface – 3 times |
| Mechanical Vibration | 10~55Hz, 1.5mm amplitude, 1 Minute Sweep 2 Hours each in 3 Directions (X, Y, Z) |
| High Temperature Burn-in | Under Power @ 125℃ for 2000 Hours (results below) |
| Hermetic Seal | He pressure: 4 ±1 kgf / cm ² 2 Hour soak |

2,000 Hour Burn-In

Burn-In Testing – under power 2000 Hours, 125℃







MTTF / FITS Calculations

Products are grouped together by process for MTTF calculations. (All XpressO output and package types are manufactured with the same process)

Number of Parts Tested: 360 (120 of each output type: HCMOS, LVDS, LVPECL)

Number of Failures:0Test Temperature:125℃Number of Hours:2000

MTTF was calculated using the following formulas:

[1.] Device Hours (devhrs) = (number of devices) x (hours at elevated temperature in %)

[2.]
$$MTTF = \frac{devhrs \times af \times 2}{\chi^2}$$

[3.] FITS =
$$\frac{1}{MTTF}$$
 * 10⁹

Where:

| A1 | T 1 (7.1 |
|---------------------|--|
| Name | Formula/Value |
| Acceleration Factor | $e^{(rac{eV}{k})	imes(rac{1}{t_1}-rac{1}{t_2})}$ |
| Activation Energy | 0.40 V |
| Bolzman's Constant | 8.62 X 10 ⁻⁵ eV/K |
| | Operating Temperature (K) |
| | Accelerated Temperature (%) |
| Theta | Confidence Level (60% industry standard) |
| Failures | Number of failed devices |
| Chi-Square | statistical significance for bivariate tabular analysis [table look-up] based on assumed Θ (Theta – confidence) and number of failures (r) For zero failures (60% Confidence): $\chi^2 = 1.830$ |
| | Activation Energy Bolzman's Constant Theta Failures |

DEVICE-HOURS = 360 x 2000 HOURS = 720,000

ACCELERATION FACTOR =
$$e^{(\frac{0.40}{8.625})\times(\frac{1}{298}-\frac{1}{398})}$$
 = 49.91009

MTTF =
$$\frac{720,000 \times 49.91009 \times 2}{1.833}$$
 = 39,209,238 Hours

Failure Rate =
$$\frac{1.833}{720,000 \times 49.91009 \times 2}$$
 = 2.55E-8

FITS = Failure Rate *1E9 = 26





Notes:

For the complete product line of XPRESSO products visit

http://www.foxonline.com/xpressomain.htm

Patent Numbers:

US 6,664,860, US 5,960,403, US 5,952,890; US 5,960,405; US 6,188,290;
Foreign Patents: R.S.A. 98/0866, R.O.C. 120851; Singapore 67081, 67082; EP 0958652
China ZL 98802217.6, Malaysia MY-118540-A, Philippines 1-1998-000245, Hong Kong #HK1026079, Mexico #232179
US and Foreign Patents Pending

XpressO™ Fox Electronics

Contact Information

(USA)-Worldwide Headquarters

Tel: 888-GET-2-FOX

Outside US: +1.239.693.0099,

Fax: +1.239.693.1554

Email: www.foxonline.com/email.htm

Fox Hong Kong

Tel: +852.2854.4285, Fax:+852.2854.4282

Email: www.foxonline.com/email.htm

Fox EMEA

Tel/Fax: +44.1767.312632

Email: www.foxonline.com/email.htm

Fox Japan

Tel: +81.3.3374.2079, Fax: +81.3.3377.5221

Email: www.foxonline.com/email.htm

Fox Taiwan

Tel:+886-2-22073427, Fax:+886-2-22073486

Email: www.foxonline.com/email.htm

The above specifications, having been carefully prepared and checked, is believed to be accurate at the time of publication; however, no responsibility is assumed by Fox Electronics for inaccuracies.

