SILICON EPITAXIAL PLANAR DIODE



1N4148D2A / 1N4148D2B

- Low Leakage
- Fast Switching
- Low Forward Voltage
- Hermetic Ceramic Surface Mount Package
- Suitable for general purpose, switching applications.
- Space Level and High-Reliability Screening Options Available



ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise stated)

| V _{BR} | Breakdown Voltage | 100V |
|------------------|---|---------------|
| V_{RWM} | Working Peak Reverse Voltage | 75V |
| lO | Average Rectified Output Current, $T_A = 75^{\circ}C^{(1)}$ | 200mA |
| I _{FSM} | Surge Current, half sine wave, $t_p = 8.3 \text{ms}^{(2)}$ | 2A |
| TJ | Junction Temperature Range | -65 to +200°C |
| T_{stg} | Storage Temperature Range | -65 to +200°C |

⁽¹⁾ I_O is rated at 200mA @ I_A = 75°C for PC boards where thermal resistance from mounting point to ambient is sufficiently controlled where T_I(Max) does not exceed 175°C

(2) $T_A = 25$ °C @ I_O =0 and VRWM for ten 8.3mS surges at 1 minute intervals.



Website: http://www.semelab-tt.com

SILICON EPITAXIAL PLANAR DIODE 1N4148D2A / 1N4148D2B



THERMAL PROPERTIES

| Symbol | Parameter | Min | Тур | Мах | Units |
|-------------------------|--|-----|-----|-----|-------|
| R _{0JA} | Thermal Resistance Junction to Ambient | | | 325 | °C/W |

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise stated)

| Symbols | Parameters | Test Condition | ons | Min. | Тур. | Max. | Units | |
|----------------|-----------------|---------------------------------------|------------------------|------|------|------|-------|--|
| V _F | Forward Voltage | I _F = 10mA | | | | 0.8 | | |
| | | I _F = 100mA | | | | 1.2 | | |
| | | $I_F = 10 \text{mA}^{(3)}$ | T _A = 150°C | | | 0.8 | V | |
| | | I _F = 100mA ⁽³⁾ | T _A = -55°C | | | 1.3 | | |
| I _R | Barrer Course | V _R = 20V | | | | 25 | 0 | |
| | | V _R = 75V | | | | 500 | nA | |
| | Reverse Current | V _R = 20V | T _A = 150°C | | | 35 | - μΑ | |
| | | V _R = 75V | 1A = 130 C | | | 75 | | |

DYNAMIC CHARACTERISTICS

| C | Capacitance | V _R = 0V | f = 1.0MHz | 4.7 | | PΓ |
|-----|-----------------------|--------------------------|-------------------|-----|---|----|
| | Сараспансе | V _R = 1.5V | 1 - 1.0101112 | 4.7 | | ρι |
| t | Reverse Recovery Time | $I_F = I_R = 10$ mA | $R_L = 100\Omega$ | | 5 | nc |
| ۲rr | Reverse Recovery Time | I _{REC} = 1.0mA | | | J | ns |

Notes


(3) Pulse Width \leq 300us, $\delta \leq$ 2%


Website: http://www.semelab-tt.com


SILICON EPITAXIAL PLANAR DIODE 1N4148D2A / 1N4148D2B



MECHANICAL DATA










DLCC2 Variant A (D2A)

| PAD 1 | ANODE | |
|-----------|------------|--------------|
| PAD 2 | CATHODE | |
| | | |
| DIMENSION | mm | Inches |
| А | 5.00 ±0.10 | 0.197 ±0.004 |
| В | 2.61 ±0.10 | 0.103 ±0.004 |
| С | 1.08 ±0.10 | 0.043 ±0.004 |
| D | 1.76 ±0.10 | 0.069 ±0.004 |






| A | |
|--------------|---|
| SML DLCC2 | В |



DLCC2 Variant B (D2B)


| PAD 1 | ANODE | | | |
|-----------|-------------|--------------|--|--|
| PAD 2 | CATHODE | | | |
| PAD 3 | LID CONTACT | TO ANODE* | | |
| | | | | |
| DIMENSION | mm | Inches | | |
| А | 5.00 ±0.10 | 0.197 ±0.004 | | |
| В | 2.61 ±0.10 | 0.103 ±0.004 | | |
| С | 1.08 ±0.10 | 0.043 ±0.004 | | |
| D | 1.76 ±0.10 | 0.069 ±0.004 | | |

DLCC2/ D-5A MELF OVERLAY



SOLDER PAD LAYOUT D-5A

| DIMENSION | mm | Inches |
|-----------|------|--------|
| А | 6.25 | 0.246 |
| В | 1.70 | 0.067 |
| C | 2.67 | 0.105 |



Website: http://www.semelab-tt.com

Other Package Outlines may be available - Contact Semelab Sales to Enquire

^{*} The additional contact provides a connection to the lid in the application. Connecting the metal lid to a known electrical potential stops deep dielectric discharge in space applications; see the Space Weather link www.semelab.co.uk/dlcc2.html on the Semelab web site. Package variant to be specified at order.

SILICON EPITAXIAL PLANAR DIODE 1N4148D2A / 1N4148D2B



SCREENING OPTIONS

Space Level (JQRS/ESA) and High Reliability options are available in accordance with the <u>High Reliability and Screening Options Handbook</u> available for download from the from the TT electronics Semelab web site.

ESA Quality Level Products are based on the testing procedures specified in the generic ESCC 5000 and in the corresponding part detail specifications.

Semelabs QR216 and QR217 processing specifications (JQRS), in conjunction with the companies ISO 9001:2000 approval present a viable alternative to the American MIL-PRF-19500 space level processing.

QR217 (Space Level Quality Conformance) is based on the quality conformance inspection requirements of MIL-PRF-19500 groups A (table V), B (table VIa), C (table VII) and also ESA / ESCC 5000 (chart F4) lot validation tests.

QR216 (Space Level Screening) is based on the screening requirements of MIL-PRF-19500 (table IV) and also ESA /ESCC 5000 (chart F3).

JQRS parts are processed to the device data sheet and screened to QR216 with conformance testing to Q217 groups A and B in accordance with MIL-STD-750 methods and procedures.

Additional conformance options are available, for example Pre-Cap Visual Inspection, Buy-Off Visit or Data Packs. These are chargeable and must be specified at the order stage (See Ordering Information). Minimum order quantities may apply.

Alternative or additional customer specific conformance or screening requirements would be considered. Contact Semelab sales with enquires.

MARKING DETAILS

Parts can be laser marked with approximately 7 characters on two lines and always includes cathode identification. Typical marking would include part or specification number, week of seal or serial number subject to available space and legibility.

Customer specific marking requirements can be arranged at the time of order.

Example Marking:



ORDERING INFORMATION

Part numbers are built up from Type, Package Variant, and screening level. The part numbers are extended to include the additional options as shown below.

Type – Main Part Number Package Variant – See Mechanical Data Screening Level – See Screening Options (ESA / JQRS)

Additional Options:

| Customer Pre-Cap Visual Inspection | .CVP |
|--|-------------------|
| Customer Buy-Off visit | .CVB |
| Data Pack | .DA |
| Solderability Samples | :SS |
| Scanning Electron Microscopy | .SEM |
| Radiography (X-ray) | .XRAY |
| Total Dose Radiation Test | .RAD |
| MIL-PRF-19500 (QR217) | |
| Group B charge | .GRPB |
| Group B destructive mechanical samples | .GBDM (12 pieces) |
| Group C charge | .GRPC |
| Group C destructive electrical samples | .GCDE (12 pieces) |
| Group C destructive mechanical samples | .GCDM (6 pieces) |
| ESA/ESCC | |
| Lot Validation Testing (subgroup 1) charge | .LVT1 |
| LVT1 destructive samples (environmental) | .L1DE (15 pieces) |
| LVT1 destructive samples (mechanical) | .L1DM (15 pieces) |
| Lot Validation Testing (subgroup 2) charge | .LVT2 |
| LVT2 endurance samples (electrical) | .L2D (15 pieces) |
| Lot Validation Testing (subgroup 3) charge | .LVT3 |
| LVT3 destructive samples (mechanical) | .L3D (5 pieces) |
| A THURST CONTRACT OF THE CONTR | |

Additional Option Notes:

- 1) All 'Additional Options' are chargeable and must be specified at order stage.
- 1) All Additional Options are chargeable and must be specified at order stage.
 2) When Group B,C or LVT is required, additional electrical and mechanical destructive samples must be ordered
- 3) All destructive samples are marked the same as other production parts unless otherwise requested.

Example ordering information:

The following example is for the 1N4148 part with package variant A, JQRS screening, additional Group C conformance testing and a Data pack.

Part Numbers:

1N4148D2A-JQRS (Include quantity for flight parts)
1N4148D2A-JQRS.GRPC (chargeable conformance option)
1N4148D2A-JQRS.GCDE (charge for destructive parts)
1N4148D2A-JQRS.GCDM (charge for destructive parts)
1N4148D2A-JQRS.DA (charge for Data pack)

Customers with any specific requirements (e.g. marking or screening) may be supplied with a similar alternative part number (there is maximum 20 character limit to part numbers). Contact Semelab sales with enquiries

High Reliability and Screening Options Handbook link: http://www.semelab.co.uk/pdf/misc/documents/hirel_and_screening_options.pdf

Semelab Limited Cove Telephone +44 (0) 1455 556565

Coventry Road, Lutterworth, Leicestershire, LE17 4JB

Document Number 8271

Issue 2