

nightingale NX

centre ward combined
circulation/lighting luminaire



Optics

- Lamp options:
 - 2 x 26W TC-D
- Low glare louvre as standard giving full glare control at the bedhead & good uniformity of illumination in circulation zone
- Provides 100 Lux daytime circulation lighting
- Night setting provides max 0.5 Lux at bedhead positions greater than 2m from luminaire with 2.6m mounting height
- Lamps are switched for night-lighting using a standard light switch (not supplied) typically at the ward entrance. This can be labelled 'Night' and 'Day'. The 'Day' position will give the 100% output required for general ward circulation lighting and the 'Night' position will give the 5 Lux required at night time. A separate mains switch is required to turn the light on and off

Body

- Analogue HF dimming gear integral to body
- Die cast aluminium bezel finished white



Lamp Performance

Wattage	IL@25°C	Lamp Life
1 x 26W TC-D	1800	13,000hrs


Order Codes

Nightingale NX	Standard	3 hr Emergency
TC-D 2 x 26W	NX24R226	NX24R226EM


Options

EASYTEST	Add suffix /ET	i.e. NX24R226/ET
COMET	Add suffix /CT	i.e. NX24R226/CT
COMEPS	Add suffix /EP	i.e. NX24R226/EP

Dimensions



Photometric Performance



Utilisation Factors UF(F)

Room Reflectance			Room Index		
C	W	F	1.00	3.00	5.00
0.70	0.50	0.20	0.37	0.47	0.50

To Specify

Die cast aluminium bodied compact fluorescent centre ward downlighter with louvre for glare control at bedhead. HF dimming gear with facility for local step dimming for night & day settings – as Whitecroft Lighting NIGHTINGALE